

Proximity Switch 8-1NC


0.0.600.05

item

Wiring Diagram







X: Threaded pin M4 x 4 DIN 551

Technical Data according to EN 60947-5-2

Electrical Data

Operational voltage range U_{B} 10 - 30V DC Rated insulation voltage 75V DC U_{i} Rated impulse withstand voltage $U_{\text{imp}} \\$ 500V Voltage drop $\leq 3.5 \text{V}$ U_{d} Utilisation category DC-13 Rated operational current $\leq 150 \text{mA}$ I_e No-load supply current ≤ 10mA I_0 IP 67 Type of protection pulsed Short-circuit protection Rated operating distance 2 mm S_n Assured operating distance 0 ... 1.6mm S_{a} Repeat accuracy R $\leq 0.22\%$ Differential travel (hysteresis) Н 1...20% max. 800Hz Switching frequency Switching function DC, N.C. Mounting flush False polarity protection

Output permanent overload and s.c.p.

Time delay before availability $t_v \leq 50 \text{ms}$

Electromagnetic compatibility (EMC) EN 60947-5-2

Mechanical Data

Operating temperature $-10^{\circ}\text{C} \dots +70^{\circ}\text{C}$

Housing

Type of connection Cable 3 x 0.14mm² x 3m; PUR - Outer jacket, grey